

## Specification Sheet

Part Number: 151-00757



Cable Tie Anchor Mount, .17" Hole Dia, .20" Max Tie Width, PEEK, Beige, 100/pkg

<b>Article Number</b>	151-00757
<b>Type</b>	CTAM1
<b>Color</b>	Beige (BGE)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Suitable for applications with minimal space.</li><li>•CTAM has 4-way entry design for use in line or at 90° angle to cable run.</li><li>•CTAM mounts are available in different sizes and materials.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.
<b>Short Description</b>	Cable Tie Anchor Mount, .17" Hole Dia, .20" Max Tie Width, PEEK, Beige, 100/pkg

**Global Part Name**

CTAM1-PEEK-BGE

**Length L (Imperial)**

0.81

**Length L (Metric)**

20.5

**Fixation Method**

Screw Mounting and Rivet

**Width W (Imperial)**

0.4

**Width W (Metric)**

10.2

**Cable Ties**

T18 - T50

**Height H (Imperial)**

0.22

**Height H (Metric)**

5.5

**Cable Tie Width Max (Imperial)**

0.2

**Cable Tie Width Max (Metric)**

5.0

**Mounting Hole Diameter D (Imperial)**

0.17

**Mounting Hole Diameter D (Metric)**

4.3 mm

**Mounting Hole Diameter D Max (Metric)**

4.3

**Material**

Polyetheretherketone (PEEK)

**Material Shortcut**

PEEK

**Flammability**

UL 94 V0

**Operating Temperature (Metric)**

-67°F to +464°F (-55°C to +240°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

100

**Package Quantity (Metric)**

100

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

2