

Specification Sheet

Part Number: 151-00765



Connector Clip w/Fir Tree, 0.6 - 6.35 mm Panel Thickness, 9.0 x 17.0 mm Hole Dia, PA66HIRHS, Black, 1000/ctn

Article Number

151-00765

Type

CC09

Color

Black (BK)

Features & Benefits

- Head design contains clamping rails to provide full circumferential compression around bundles.
- Bent tail allows for quick insertion into head.

Quantity Per

carton

Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description	Connector Clip w/Fir Tree, 0.6 - 6.35 mm Panel Thickness, 9.0 x 17.0 mm Hole Dia, PA66HIRHS, Black, 1000/ctn
Global Part Name	CC09-PA66HIRHS-BK
Length L (Imperial)	1.30
Length L (Metric)	33.05
Fixation Method	Fir Tree
Width W (Imperial)	0.85
Width W (Metric)	21.59
Height H (Imperial)	0.76
Height H (Metric)	19.4
Panel Thickness Min(Imperial)	0.019
Panel Thickness Max(Imperial)	0.252
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	6.4
Mounting Hole Diameter D (Imperial)	0.35 x 0.67
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35

Mounting Hole Diameter D Max (Imperial)	0.67
--	------

Mounting Hole Diameter D Max (Metric)	17.0
--	------

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
-----------------	--

Material Shortcut	PA66HIRHS
--------------------------	-----------

Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
---------------------------------------	-----------------------------------

Reach Complaint(Article 33)	Yes
------------------------------------	-----

ROHS Complaint	Yes
-----------------------	-----

Package Quantity(Imperial)	1000
-----------------------------------	------

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number	3926909988
-----------------------	------------

Content Unit(BMEcat)	pcs.
-----------------------------	------