

Specification Sheet

Part Number: 151-00927



Fir Tree C-Clip, .24"-.30" Bundle Dia, .03"-.25" Panel, .26" Mnt Hole, PA66HIRHSUV, Black, 100/pkg

Article Number	151-00927
Type	SC6.6
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Pre-drilled holes allows for Easy installation by hand.• Cable can be removed and reinstalled without removing the clip, providing multiple use options.• Made of PA66HIRHSUV material for withstanding extreme conditions
Quantity Per	bag

Product Description

The C Clip with fir tree mount is ideal for panels with pre-drilled holes. Easy installation by hand eliminates the need for any tools. Once installed, the cable simply snaps into the clip. The cable can be removed and reinstalled without removing the clip. Made from PA66HIRHSUV material, the clip offers increased flexibility along with heat resistance and UV stability.

Short Description

Fir Tree C-Clip, .24"-.30" Bundle Dia, .03"-.25" Panel, .26" Mnt Hole, PA66HIRHSUV, Black, 100/pkg

Global Part Name

SC6.6-PA66HIRHSUV-BK

Width W (Imperial)

0.72

Width W (Metric)

18.26

Bundle Diameter Min (Imperial)

0.24

Bundle Diameter Min (Metric)

6.0

Bundle Diameter Max (Imperial)

0.29

Bundle Diameter Max (Metric)

7.6

Height H (Imperial)

1.32

Height H (Metric)

33.43

Panel Thickness Min(Imperial)

0.03

Panel Thickness Max(Imperial)

0.25

Panel Thickness Min (Metric)

0.7

Panel Thickness Max (Metric)

6.35

Mounting Hole Diameter D (Imperial)

0.26

Mounting Hole Diameter D (Metric)

6.6 mm

Mounting Hole Diameter D Max (Metric)

6.6

Disc Diameter(Metric)

18.55

Disc Diameter (Imperial)

0.73

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Operating Temperature (Metric)

-65°F to +230°F (-54°C to +110°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

