

Specification Sheet

Part Number: 151-01199

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.



HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.

Connector Clipwith Oval Fir Tree, 12.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 4000/carton

Article Number 151-01199

Type CC15

Color Black (BK)

Quantity Per carton

Product Description

Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Short Description	Connector Clipwith Oval Fir Tree, 12.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 4000/carton
Global Part Name	CC15-PA66HIRHSUV-BK
Length L (Imperial)	1.19
Length L (Metric)	30.3
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.80
Width W (Metric)	20.3
Height H (Imperial)	0.93
Height H (Metric)	23.6
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.35
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	9.0
Mounting Hole Diameter D (Imperial)	0.47 x 0.67
Mounting Hole Diameter D (Metric)	12.0 x 17.0 mm
Mounting Hole Diameter D Min (Imperial)	0.47

Mounting Hole Diameter D Max (Imperial)	0.47
Mounting Hole Diameter D Max (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.

www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)