

Specification Sheet

Part Number: 151-01310



Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg

Article Number	151-01310
Type	DUALFT6DOCK
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Fir Tree demonstrates easy insertion with high extraction resistance in 6.5 +/- 0.4 mm hole.• C-clip design allows for multiple uses, from hoses and tubes to harnesses and cables.
Quantity Per	carton

Product Description

HellermannTyton connector clips for oval holes are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times. Dual routing clip provides a secure fit for two routings between 12 - 15 mm diameter.

Short Description	Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg
Global Part Name	DUALFT6DOCK-PA66HIRHSUV-BK
Length L (Imperial)	2.04
Length L (Metric)	51.8
Width W (Imperial)	0.66
Width W (Metric)	16.66
Height H (Imperial)	1.36
Height H (Metric)	34.63
Nominal Diameter (Metric)	15.5
Panel Thickness Min(Imperial)	0.02
Panel Thickness Max(Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.5 mm
Mounting Hole Diameter D Max (Metric)	6.9

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988
Weight (Metric)	6.53
Weight (Imperial)	14.39