

Specification Sheet

Part Number: 151-01631



VHB Adhesive Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66HIRHSUV, Black, 100/pkg

Article Number

151-01631

Type

MB4A

Color

Black (BK)

Features & Benefits

- For use with 18 through 50 pound HellermannTyton cable ties.
- Extremely durable adhesive achieves high pull-off force and is unaffected by vibration.
- Multiple sizes accommodate a range of cable ties.
- 4-way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
- Predrilled holes extend mounting options and security.
- Mount made of proprietary, impact-modified PA66 material for extraordinary durability, and is heat stabilized and UV resistant for extended life outdoors.
- Peel and stick for quick, convenient use in extreme-duty applications.

Quantity Per

bag

Product Description

HellermannTyton offers adhesive mounts in a variety of sizes to match your cable tie size and extreme-duty application needs. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.

Short Description

VHB Adhesive Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66HIRHSUV, Black, 100/pkg

Global Part Name

MB4A-PA66HIRHSUV-BK

Length L (Imperial)

1.12

Length L (Metric)

28.5

Fixation Method

Adhesive

Width W (Imperial)

1.12

Width W (Metric)

28.5

Cable Ties

T18 - T50

Height H (Imperial)

.22

Height H (Metric)

5.60

Cable Tie Width Max (Imperial)

0.18

Cable Tie Width Max (Metric)

4.6

Mounting Hole Diameter D (Imperial)

0.18

Mounting Hole Diameter D (Metric)

4.6 mm

Mounting Hole Diameter D Min (Imperial)	0.18
--	------

Mounting Hole Diameter D Max (Imperial)	0.18
--	------

Mounting Hole Diameter D Max (Metric)	4.6
--	-----

Mounting Hole Centers (Imperial)	0.8
---	-----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
-----------------	--

Material Shortcut	PA66HIRHSUV
--------------------------	-------------

Adhesive	Acrylic foam
-----------------	--------------

Flammability	UL 94 HB
---------------------	----------

Operating Temperature (Metric)	-40°F to +176°F (-40°C to +80°C)
---------------------------------------	----------------------------------

ROHS Complaint	Yes
-----------------------	-----

Package Quantity(Imperial)	100
-----------------------------------	-----

Package Quantity (Metric)	100
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

