

Specification Sheet

Part Number: 151-01634



VHB Adhesive Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66HIRHSUV, Black, 250/pkg

Article Number

151-01634

Type

MB5A

Color

Black (BK)

Features & Benefits

- For use with 18 through 150 pound HellermannTyton cable ties.
- Extremely durable adhesive achieves high pull-off force and is unaffected by vibration.
- Multiple sizes accommodate a range of cable ties.
- 4-way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
- Pre-drilled holes extend mounting options and security.
- Mount made of proprietary, impact-modified PA66 material for extraordinary durability, and is heat stabilized and UV resistant for extended life outdoors.
- Peel and stick for quick, convenient use in extreme-duty applications.

Quantity Per

bag

Product Description

HellermannTyton offers adhesive mounts in a variety of sizes to match your cable tie size and extreme-duty application needs. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.

Short Description

VHB Adhesive Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66HIRHSUV, Black, 250/pkg

Global Part Name

MB5A-PA66HIRHSUV-BK

Length L (Imperial)

1.49

Length L (Metric)

37.7

Fixation Method

Adhesive

Width W (Imperial)

1.49

Width W (Metric)

37.7

Cable Ties

T18 - T150

Height H (Imperial)

.28

Height H (Metric)

7.10

Cable Tie Width Max (Imperial)

0.35

Cable Tie Width Max (Metric)

8.9

Mounting Hole Diameter D (Imperial)

0.19

Mounting Hole Diameter D (Metric)

4.8 mm

Mounting Hole Diameter D Min (Imperial)	0.19
--	------

Mounting Hole Diameter D Max (Imperial)	0.19
--	------

Mounting Hole Diameter D Max (Metric)	4.8
--	-----

Mounting Hole Centers (Imperial)	1
---	---

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
-----------------	--

Material Shortcut	PA66HIRHSUV
--------------------------	-------------

Adhesive	Acrylic foam
-----------------	--------------

Flammability	UL 94 HB
---------------------	----------

Operating Temperature (Metric)	-40°F to +176°F (-40°C to +80°C)
---------------------------------------	----------------------------------

ROHS Complaint	Yes
-----------------------	-----

Package Quantity(Imperial)	250
-----------------------------------	-----

Package Quantity (Metric)	250
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

