

Specification Sheet

Part Number: 151-01740



MOC Clip, 9 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 1000/ctn

Article Number	151-01740
Type	MOC9FT6.5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Fir tree demonstrates easy insertion with high extraction resistance.
Quantity Per	carton
Product Description	The MOC with Round Fir Tree features HellermannTyton's unique retention clip with an integrated fir tree to fit securely in a 6.5 (+/-0.4) mm hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel.
Short Description	MOC Clip, 9 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC9FT6.5-PA66HIRHSUV-BK

Length L (Imperial)

0.67

Length L (Metric)

17.0

Fixation Method

Fir Tree

Bundle Diameter Min (Imperial)

0.31

Bundle Diameter Min (Metric)

8.0

Bundle Diameter Max (Imperial)

0.39

Bundle Diameter Max (Metric)

10.0

Height H (Imperial)

1.30

Height H (Metric)

33.1

Depth D (imperial)

0.39

Depth D (metric)

10.0

Panel Thickness Min(Imperial)

0.02

Panel Thickness Max(Imperial)

0.22

Panel Thickness Min (Metric)

0.60

Panel Thickness Max (Metric)

5.5

Mounting Hole Diameter D (Imperial)

0.25 " HEX; 0.26

Mounting Hole Diameter D (Metric)	6.35 mm (hexagonal) 6.5 mm (+/- 0.4 mm)
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	1.02
Weight (Imperial)	0.04

