

Specification Sheet

Part Number: 151-01788



MOC Clip, 19 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 3000/ctn

Article Number	151-01788
Type	MOC19FT6.5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Fir tree demonstrates easy insertion with high extraction resistance.
Quantity Per	carton
Product Description	The MOC with Round Fir Tree features HellermannTyton's unique retention clip with an integrated fir tree to fit securely in a 6.5 (+/-0.4) mm hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel.
Short Description	MOC Clip, 19 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 3000/ctn

Global Part Name

MOC19FT6.5-PA66HIRHSUV-BK

Length L (Imperial)

1.07

Length L (Metric)

27.3

Fixation Method

Fir Tree

Bundle Diameter Min (Imperial)

0.67

Bundle Diameter Min (Metric)

17.0

Bundle Diameter Max (Imperial)

0.86

Bundle Diameter Max (Metric)

21.8

Height H (Imperial)

1.91

Height H (Metric)

48.5

Depth D (imperial)

0.47

Depth D (metric)

12.0

Panel Thickness Min(Imperial)

0.02

Panel Thickness Max(Imperial)

0.22

Panel Thickness Min (Metric)

0.60

Panel Thickness Max (Metric)

5.5

Mounting Hole Diameter D (Imperial)

0.25 " HEX; 0.26

Mounting Hole Diameter D (Metric)

6.5 mm (+/- 0.4 mm) 6.35 mm (hexagonal)

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

3000

Package Quantity (Metric)

3000

Customs Number

3926909988

Weight (Metric)

3.33

Weight (Imperial)

0.12

