

Specification Sheet

Part Number: 151-01883



Bundling Clip w/Oval Fir Tree, 2.28" Long, 0.02-0.10" Panel Thickness, PA66HIRHS, Natural, 8000/ctn

Article Number	151-01883
Type	BCSFTOVAL
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.
Quantity Per	carton
Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
Short Description	Bundling Clip w/Oval Fir Tree, 2.28" Long, 0.02-0.10" Panel Thickness, PA66HIRHS, Natural, 8000/ctn

Global Part Name

BCSFTOVAL-PA66HIRHSUV-NA

Length L (Imperial)

2.28

Length L (Metric)

58.0

Fixation Method

Fir Tree for oval holes

Width W (Imperial)

0.30

Width W (Metric)

7.62

Height H (Imperial)

0.46

Height H (Metric)

11.6

Panel Thickness Min(Imperial)

0.02

Panel Thickness Max(Imperial)

0.10

Panel Thickness Min (Metric)

0.6

Panel Thickness Max (Metric)

2.5

Mounting Hole Diameter D (Imperial)

0.24 x 0.48 " 0.25 x 0.50 " 0.25 x 0.50 " 0.27 x 0.47

Mounting Hole Diameter D (Metric)

6.5 x 12.5 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.2 x 12.2 mm

Mounting Hole Diameter D Min (Imperial)

0.24

Mounting Hole Diameter D Max (Imperial)

0.51

Mounting Hole Diameter D Max (Metric)

13.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	8000
Package Quantity (Metric)	8000
Customs Number	3926909988
Content Unit(BMEcat)	pcs.