

## Specification Sheet

Part Number: 151-02094



High Torque Mount, Mounting Hole Dia. 0.327", Max Torque 114.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

Article Number	151-02094
Type	HDM320
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Mount and tie combination makes it easy to service bundles in the field.</li><li>• Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.</li><li>• Eliminates the needs for multiple sized fix diameter clamps.</li></ul>
Quantity Per	carton

### Product Description

The high-torque mount is designed for use with power-assisted impact wrenches and is molded with a heavy bushing to withstand the forces required to tighten grade 8 bolts. The arched H-profile of the saddle surface allows for a broad surface contact with the bundle, minimizing pinching and crushing of the bundles, and adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

**Short Description**

High Torque Mount, Mounting Hole Dia. 0.327", Max Torque 114.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

**Global Part Name**

HDM320-PA66HIRHSUV-BK

**Length L (Imperial)**

1.85

**Length L (Metric)**

47.0

**Fixation Method**

Screw Mounting and Rivet

**Width W (Imperial)**

1.0

**Width W (Metric)**

25.0

**Height H (Imperial)**

0.81

**Height H (Metric)**

20.7

**Cable Tie Width Max (Imperial)**

0.5

**Cable Tie Width Max (Metric)**

12.7

**Mounting Hole Diameter D (Imperial)**

0.327

**Mounting Hole Diameter D (Metric)**

8.31 mm

**Mounting Hole Diameter D Min (Imperial)**

0.327

**Mounting Hole Diameter D Max (Imperial)**

0.327

**Mounting Hole Diameter D Max (Metric)**

8.31

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>Maximum Torque (kgf-cm)</b>	1576.0
<b>Maximum Torque (lbf-ft)</b>	114.0
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.
<b>Weight (Metric)</b>	0.0202
<b>Weight (Imperial)</b>	0.0446

