

Specification Sheet

Part Number: 151-02099



High Torque Axial Mount, Bolt Hole Dia. 0.327", PA66HIRHSUV, Black, 500/pkg

Article Number	151-02099
Type	SAM320B-R
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Positions bundles off cross members and frame rails to prevent abrasion and chafing.• Metal insert bushing accommodates high-torque installation.• Made with high-impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.
Quantity Per	carton

Product Description

HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.

Short Description

High Torque Axial Mount, Bolt Hole Dia. 0.327", PA66HIRHSUV, Black, 500/pkg

Global Part Name

SAM320B-R-PA66HIRHSUV-BK

Length L (Imperial)

1.18

Length L (Metric)

29.9

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

1.0

Width W (Metric)

25.0

Height H (Imperial)

1.77

Height H (Metric)

44.9

Mounting Hole Diameter D (Imperial)

0.327

Mounting Hole Diameter D (Metric)

8.31 mm

Mounting Hole Diameter D Min (Imperial)

0.327

Mounting Hole Diameter D Max (Imperial)

0.327

Mounting Hole Diameter D Max (Metric)

8.31

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.0198

Weight (Imperial)

0.0437