

Specification Sheet

Part Number: 151-02436



Low Profile Metal Edge Clip, 1.5–2.0mm Panel Thickness, 4.1–7mm Cable Range, SS304, 5000/box

Article Number	151-02436
Type	MSC2LP
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">•Integrated design allows for easy insertion by hand.•1.5–2.0mm panel thickness range allows for multiple applications.•Double-compression design that accommodates various sizes of wire and cable.•Presents a high extraction force for withstanding extreme conditions.
Quantity Per	box

Product Description

Designed for more confined areas, HellermannTyton's Low Profile Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Short Description	Low Profile Metal Edge Clip, 1.5–2.0mm Panel Thickness, 4.1–7mm Cable Range, SS304, 5000/box
Global Part Name	MSC2LP-SS304-ML
Length L (Imperial)	0.67
Length L (Metric)	17.0
Width W (Imperial)	0.375
Width W (Metric)	9.50
Panel Thickness Min(Imperial)	0.06
Panel Thickness Max(Imperial)	0.078
Panel Thickness Min (Metric)	1.5
Panel Thickness Max (Metric)	2.0
Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen free	No
Operating Temperature (Metric)	-112°F to +1000°F (-80°C to +538°C)
Reach Complaint(Article 33)	Yes

ROHS Complaint Yes

UL Recognized (US) Yes

UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes

UL Listed (US) Yes

Package Quantity(Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 7326908695

Content Unit(BMEcat) pcs.

Weight (Metric) 0.00256

Weight (Imperial) 0.00564