

Specification Sheet

Part Number: 151-02551



USCAR Connector Clip with I-beam Bundling Clip, 11mm, POM, Black, 5000/ctn

Article Number

151-02551

Type

SOC25SO9CC11

Color

Black (BK)

Features & Benefits

- Connector Clip with tape bar secures connectors with USCAR 11 mm slot and provides strain relief for the connector and wiring assembly.
- Compact I-beam design provides a robust solution for all bundles, small to large.
- Dog bone ends help secure tape or tie, preventing bundling clip from slipping off bundle.
- Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.
- Meets installation and extraction requirements of SAE/USCAR-2, for easy insertion and reliable performance.

Quantity Per

carton

Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description

USCAR Connector Clip with I-beam Bundling Clip, 11mm, POM, Black, 5000/ctn

Global Part Name

SOC25SO9CC11-POM-BK

Length L (Imperial)

1.96

Length L (Metric)

50.0

Width W (Imperial)

0.427

Width W (Metric)

10.85

Height H (Imperial)

0.539

Height H (Metric)

13.7

Material

Polyacetal (POM)

Material Shortcut

POM

Operating Temperature (Metric)

-40°F to +194°F (-40°C to +90°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

5000

Package Quantity (Metric)

5000

Customs Number

3926909988