

Specification Sheet

Part Number: 151-02587



Mini Channel, 70mm Long, 120 degree, 17.1mm radius angle, PA66HIRHSUV, Black, 1000/ctn

Article Number

151-02587

Type

120MINICHNLFT6.5

Color

Black (BK)

Features & Benefits

- Channel gradually bends bundles at 120-degree angle around corners and or obstructions to avoid wire bundle strain.
- L-shape channel provides protection and support for wire or bundle.
- Tie slots and guides in multiple locations help locate and secure cable ties to prevent slipping.
- 6.5 mm fir tree enables mounting.
- Protects against abrasion and other environmental factors.

Quantity Per

carton

Product Description

The Mini Channel family provides a cost-effective, protective, configurable routing solution. Pieces are modular and interchangeable, allowing extensive customization. Mini Channels replace engineered channels that are costly to design and develop.

Short Description

Mini Channel, 70mm Long, 120 degree, 17.1mm radius angle, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

120MINICHNLFT6.5-PA66HIRHSUV-BK

Length L (Imperial)

3.01

Length L (Metric)

76.53

Width W (Imperial)

0.765

Width W (Metric)

19.44

Mounting Hole Diameter D (Imperial)

0.255

Mounting Hole Diameter D (Metric)

6.5 mm

Material

Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)