

Specification Sheet

Part Number: 151-02646



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple configurations to mount to a variety of surfaces

Releaseable to allow for maintenance

Conduit Clamps, Size 25, Mounting Hole 8.8 mm, Offset 40.5 mm, PA66HIRHS, Black, 500/pkg

Article Number 151-02646

Type CDC25R40.5M8

Color Black (BK)

Quantity Per carton

Product Description The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters.

Short Description Conduit Clamps, Size 25, Mounting Hole 8.8 mm, Offset 40.5 mm, PA66HIRHS, Black, 500/pkg

Global Part Name CDC25R40.5M8-PA66HIRHS-BK

Length L (Imperial) 3.83

Length L (Metric) 97.3

Offset Length (Imperial) 1.59

Offset Length (Metric) 40.5

Fixation Method screwable

Width W (Imperial) 0.9

Width W (Metric) 22

Bundle Diameter Max (Imperial) 0.98

Bundle Diameter Max (Metric) 25.0

Height H (Imperial) 3.43

Height H (Metric) 87.1

Diameter D (Imperial) 1.06

Diameter D (Metric) 27.0

Mounting Hole Diameter D (Imperial) 0.35

Mounting Hole Diameter D (Metric) 8.8 mm

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	M8
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)