

Specification Sheet

Part Number: 151-02875



Series 6 RPC Hanger, 0.5 - 0.77" Dia, 0.22" Mounting Hole Dia, PA66HIRHSUV/ST/ZN, Black, 280/ctn

Article Number

151-02875

Type

RCBHANGER

Color

Black (BK)

Features & Benefits

- Impact modified, heat and UV stabilized PA66 provides long-term durability in solar applications.
- One-piece ratchet closure design allows for easy installation during pre- or final assembly.
- Release feature allows for quick adjustments and maintenance.
- First Solar specific steel mounting hanger tolerates high torque and is treated to resist chemicals.

Quantity Per

box

Product Description

The Series 6 Ratchet P-Clamp Solar Hanger offers one-handed, toolless simplicity and size versatility for managing wires and cables on First Solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. The one-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes of fixed diameter fasteners. The integrated release feature enables easy and nondestructive removal of cables by inserting a flat-head screwdriver. This allows the clamp to be reused without removing it.

Short Description

Series 6 RPC Hanger, 0.5 - 0.77" Dia, 0.22" Mounting Hole Dia, PA66HIRHSUV/ST/ZN, Black, 280/ctn

Global Part Name

RCBHANGER-PA66HIRHSUV/ZN-BK

Minimum Tensile Strength (Imperial)

100.0

Minimum Tensile Strength (Metric)

445.0

Length L (Imperial)

4.54

Length L (Metric)

115.4

Fixation Method

Screw Mounting

Variant

Fixing clamp

Width W (Imperial)

1.37

Width W (Metric)

34.9

Bundle Diameter Min (Imperial)

0.5

Bundle Diameter Min (Metric)

12.7

Bundle Diameter Max (Imperial)

0.77

Bundle Diameter Max (Metric) 19.5

Height H (Imperial) 1.37

Height H (Metric) 34.9

Mounting Hole Diameter D (Imperial) 0.22

Mounting Hole Diameter D (Metric) 5.6 mm

Material Zinc plated (ZN) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut ZN PA66HIRHSUV

UV Resistant (Yes/No) Yes

Operating Temperature (Metric) -40°F to +230°F (-40°C to +110°C)

ROHS Complaint Yes

UL Listed (US and Canada) Yes

UL Listed (US) Yes

Package Quantity(Imperial) 280

Package Quantity (Metric) 280

Customs Number 3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)