

Specification Sheet

Part Number: 151-02896

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.



HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.

Connector Clip with Oval Fir Tree, 0.60 - 6.0 mm Panel Thickness, 9x17mm Hole, PPS, Silver, 5000/ctn

Article Number 151-02896

Type CC11B

Color Silver (SR)

Quantity Per bag

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Connector Clip with Oval Fir Tree, 0.60 - 6.0 mm Panel Thickness, 9x17mm Hole, PPS, Silver, 5000/ctn

Global Part Name CC11B-PPS-SR

Length L (Imperial) 1.18

Length L (Metric) 30.0

Fixation Method Fir Tree for oval holes

Width W (Imperial) 0.72

Width W (Metric) 18.20

Height H (Imperial) 0.81

Height H (Metric) 20.60

Panel Thickness Min (Imperial) 0.02

Panel Thickness Max (Imperial) 0.23

Panel Thickness Min (Metric) 0.6

Panel Thickness Max (Metric) 6.0

Mounting Hole Diameter D (Imperial) 0.35 x 0.67

Mounting Hole Diameter D (Metric) 9.0 x 17.0 mm

Mounting Hole Diameter D Min (Imperial) 0.7

Mounting Hole Diameter D Max (Imperial) 0.7

Mounting Hole Diameter D Max (Metric)	9.0
Material	Polyphenylene Sulfide (PPS)
Material Shortcut	PPS
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

