

Specification Sheet

Part Number: 151-03402



Edge Clip and Tape Clip, Panel Thickness 0.04" - 0.12", 1.6" Long, PA66HIRHS, Black, 500/pkg

Article Number

151-03402

Type

EC16

Color

Black (BK)

Features & Benefits

- Edge clip applies easily to plastic and metal edges without the need for a mounting hole.
- Tape bar provides a convenient surface for securing a bundle using a cable tie or tape.

Quantity Per

bag

Product Description

HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description	Edge Clip and Tape Clip, Panel Thickness 0.04" - 0.12", 1.6" Long, PA66HIRHS, Black, 500/pkg
Global Part Name	EC16-PA66HIRHS-BK
Length L (Imperial)	1.6
Length L (Metric)	40.0
Fixation Method	with EdgeClip (Mounts)
Width W (Imperial)	0.39
Width W (Metric)	10.0
Height H (Imperial)	0.51
Height H (Metric)	13.0
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS

Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.2