

Specification Sheet

Part Number: 151-10904



Q Tie Mount with Adhesive, 0.79" x 0.79" x 0.17", 4 way entry for Q18 - Q30 ties, PA66, White, 100/bag

Article Number	151-10904
Type	QM20A
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• 2- or 4-way entry options for the Q Tie, offering flexibility and stability
Quantity Per	bag
Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
Short Description	Q Tie Mount with Adhesive, 0.79" x 0.79" x 0.17", 4 way entry for Q18 - Q30 ties, PA66, White, 100/bag

Global Part Name

QM20A-PA66-NA

Length L (Imperial)

0.79

Length L (Metric)

20.0

Fixation Method

Screw Mounting and Adhesive

Width W (Imperial)

0.79

Width W (Metric)

20.0

Height H (Imperial)

0.17

Height H (Metric)

3.7

Cable Tie Width Max (Imperial)

0.14

Cable Tie Width Max (Metric)

4.0

Mounting Hole Diameter D (Imperial)

0.12

Mounting Hole Diameter D (Metric)

3.1 mm

Mounting Hole Diameter D Min (Imperial)

0.12

Mounting Hole Diameter D Max (Metric)

3.1

Mounting Hole Centers (Imperial)

0.53

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V2 (excluding adhesive)
Halogen free	Yes
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.