

## Specification Sheet

Part Number: 151-10930



Q Tie Mount, M4 Screw, 0.83" x 0.38" x 0.26", For Q18–Q50 ties, PA66, Black, 100/bag

Article Number	151-10930
Type	CTQM5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•2- or 4-way entry options for the Q-Tie, offering flexibility and stability</li><li>•Designed for use with 18- through 120-pound cable ties to provide stability when securing bundles.</li><li>•Secures with a single screw, providing quick installation.</li></ul>
Quantity Per	bag

### Product Description

Q-Series mounting bases are designed to work exclusively with the Q-Tie® cable tie series. This mounting component can be secured with screws. The Q-Mount allows either a two- or four-way entry for the Q-Tie, providing a quick and simple insertion into the mount. Once in place, the Q-Tie will not slip out, even in vertical mounting applications.

<b>Short Description</b>	Q Tie Mount, M4 Screw, 0.83" x 0.38" x 0.26", For Q18–Q50 ties, PA66, Black, 100/bag
<b>Global Part Name</b>	CTQM5-PA66-BK
<b>Length L (Imperial)</b>	0.83
<b>Length L (Metric)</b>	21.0
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.38
<b>Width W (Metric)</b>	9.5
<b>Cable Ties</b>	Q-Ties
<b>Height H (Imperial)</b>	0.26
<b>Height H (Metric)</b>	6.7
<b>Cable Tie Width Max (Imperial)</b>	0.2
<b>Cable Tie Width Max (Metric)</b>	5.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.175
<b>Mounting Hole Diameter D (Metric)</b>	4.5 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.18
<b>Mounting Hole Diameter D Max (Metric)</b>	4.5

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL   ANSI/UL 746B UL   ANSI/UL 62275 UL   ANSI/UL 1565
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.

