

Specification Sheet

Part Number: PC15FT7



Fir Tree Mount Tube Clip Mounting Hole Dia .25" Panel Thickness .12" PA66HIRHS, Black 1000/box

Article Number	151-14303
Type	PC15FT7
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Clip is designed for fixation and bundling of tubes and pipes.
Quantity Per	bag
Product Description	Designed to offer a durable single-hole mounting, this tube clip allows the installer to insert the fir tree with minimal force while providing a secure hold.
Short Description	Fir Tree Mount Tube Clip Mounting Hole Dia .25" Panel Thickness .12" PA66HIRHS, Black 1000/box
Global Part Name	PC15FT7-PA66HIRHSUV-BK

Length L (Imperial)	0.62
Length L (Metric)	15.75
Fixation Method	Fir Tree
Width W (Imperial)	0.85
Width W (Metric)	21.6
Bundle Diameter Max (Imperial)	0.62
Bundle Diameter Max (Metric)	15.7
Height H (Imperial)	1.5
Height H (Metric)	38.1
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.31
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.27
Mounting Hole Diameter D (Metric)	6.4 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.27

Mounting Hole Diameter D Max (Metric) 6.8

Disc Diameter(Metric) 21.6

Disc Diameter (Imperial) 0.9

Material Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL 94 HB

Operating Temperature (Metric) -40°F to +230°F (-40°C to +110°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Package Quantity(Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

Content Unit(BMEcat) pcs.

