

Specification Sheet

Part Number: 151-15500



Flat Ribbon Cable Clamp, Adhesive, 2.22" Hole Dia, PA66HIR, Black, 100/pkg

Article Number	151-15500
Type	FKH50A
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable.• Releasable for easy access to cables when necessary.• Available in adhesive or screw-mount versions.
Quantity Per	pcs.

Product Description

HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary. These clamps are available in adhesive or screw mount versions.

Short Description	Flat Ribbon Cable Clamp, Adhesive, 2.22" Hole Dia, PA66HIR, Black, 100/pkg
Global Part Name	FKH50A-PA66HIR-BK
Length L (Imperial)	2.22
Length L (Metric)	56.5
Fixation Method	Pasting / Stick
Variant	Mounting clip
Width W (Imperial)	0.98
Width W (Metric)	25.0
Mounting Hole Diameter D (Imperial)	0.122
Mounting Hole Diameter D (Metric)	3.1 mm
Mounting Hole Diameter D Min (Imperial)	0.122
Mounting Hole Diameter D Max (Imperial)	0.122
Mounting Hole Diameter D Max (Metric)	3.1
Material	Polyamide 6.6, high impact modified (PA66HIR)
Material Shortcut	PA66HIR

Adhesive	Acrylate with base of polyurethane foam
Flammability	UL 94 HB (excluding adhesive)
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	to +221°F (+105°C)
Operating Temperature (Metric)	-40°F to +176°F (-40°C to +80°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	6.8