

## Specification Sheet

Part Number: MB4A0H4



Adhesive Cable Tie Mount, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66/Rubber, Black, 500/pkg

Article Number	151-28406
Type	MB4A
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Durable adhesive achieves high pull-off force and is unaffected by vibration.</li><li>•4-way opening allows cable ties to be installed parallel or perpendicular to bundles.</li><li>•Predrilled holes extend mounting options and security.</li><li>•Extended adhesive liner is easy to remove quickly.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton Adhesive Cable Tie Mounting Bases are used with T18 through T150 Series cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4-way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles. Rubber-based adhesive allows for a permanent bond to most surfaces.

<b>Short Description</b>	Adhesive Cable Tie Mount, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66/Rubber, Black, 500/pkg
<b>Global Part Name</b>	MB4A-PA66-BK
<b>Length L (Imperial)</b>	1.12
<b>Length L (Metric)</b>	28.5
<b>Fixation Method</b>	Screw Mounting and Adhesive
<b>Width W (Imperial)</b>	1.12
<b>Width W (Metric)</b>	28.5
<b>Cable Ties</b>	T18 - T50
<b>Height H (Imperial)</b>	.22
<b>Height H (Metric)</b>	5.60
<b>Cable Tie Width Max (Imperial)</b>	0.18
<b>Cable Tie Width Max (Metric)</b>	4.6
<b>Mounting Hole Diameter D (Imperial)</b>	0.18
<b>Mounting Hole Diameter D (Metric)</b>	4.6 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	4.6
<b>Mounting Hole Centers (Imperial)</b>	0.8

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Adhesive</b>	Synthetic rubber with base of polyethylene foam
<b>Flammability</b>	UL 94 V2 (excluding adhesive)
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988