

## Specification Sheet

Part Number: MB4A10A2C2



Adhesive Cable Tie Mount, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66, White, 100/pkg

**Article Number**

151-28420

**Type**

MB4A

**Color**

White (WH)

**Features & Benefits**

- For use with 18 and 30 pound cable ties to provide stability when securing bundles.
- Secures with rubber based adhesive backing and/or two or four screws.
- 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.

**Quantity Per**

bag

**Product Description**

HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

<b>Short Description</b>	Adhesive Cable Tie Mount, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66, White, 100/pkg
<b>Global Part Name</b>	MB4A-PA66-WH
<b>Length L (Imperial)</b>	1.12
<b>Length L (Metric)</b>	28.5
<b>Fixation Method</b>	Screw Mounting and Adhesive
<b>Width W (Imperial)</b>	1.12
<b>Width W (Metric)</b>	28.5
<b>Cable Ties</b>	T18 - T50
<b>Height H (Imperial)</b>	.23
<b>Height H (Metric)</b>	5.80
<b>Cable Tie Width Max (Imperial)</b>	0.18
<b>Cable Tie Width Max (Metric)</b>	4.6
<b>Mounting Hole Diameter D (Imperial)</b>	0.18
<b>Mounting Hole Diameter D (Metric)</b>	4.6 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	4.6
<b>Mounting Hole Centers (Imperial)</b>	0.8

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Adhesive</b>	Acrylate with base of acrylic foam
<b>Flammability</b>	UL 94 V2 (excluding adhesive)
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988