

## Specification Sheet

Part Number: MB50F4



Screw Mount Cable Tie Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66, Black, 250/pkg

<b>Article Number</b>	151-28501
<b>Type</b>	MB5
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Compact size fits most mounting applications.</li><li>•Simple to install with a screw or rivet.</li><li>•Single hole attachment with two-way entry for cable tie.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.
<b>Short Description</b>	Screw Mount Cable Tie Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66, Black, 250/pkg

**Global Part Name**

MB5-PA66-BK

**Length L (Imperial)**

1.49

**Length L (Metric)**

37.7

**Fixation Method**

Screw Mounting and Rivet

**Width W (Imperial)**

1.49

**Width W (Metric)**

37.7

**Cable Ties**

T18 - T150

**Height H (Imperial)**

.25

**Height H (Metric)**

6.20

**Cable Tie Width Max (Imperial)**

0.35

**Cable Tie Width Max (Metric)**

8.9

**Mounting Hole Diameter D (Imperial)**

0.19

**Mounting Hole Diameter D (Metric)**

4.8 mm

**Mounting Hole Diameter D Max (Metric)**

4.8

**Mounting Hole Centers (Imperial)**

1.0

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	250
<b>Package Quantity (Metric)</b>	250
<b>Customs Number</b>	3926909988