

Specification Sheet

Part Number: MB5A0C2



Adhesive Cable Tie Mount, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66/SR T50, Black, 100/pkg

Article Number

151-28602

Type

MB5A

Color

Black (BK)

Features & Benefits

- Durable adhesive achieves high pull-off force and is unaffected by vibration.
- 4-way opening allows cable ties to be installed parallel or perpendicular to bundles.
- Predrilled holes extend mounting options and security.
- Extended adhesive liner is easy to remove quickly.

Quantity Per

bag

Product Description

HellermannTyton Adhesive Cable Tie Mounting Bases are used with T18 through T150 Series cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4-way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles. Rubber-based adhesive allows for a permanent bond to most surfaces.

Short Description	Adhesive Cable Tie Mount, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66/SR T50, Black, 100/pkg
Global Part Name	MB5A-PA66-BK
Length L (Imperial)	1.49
Length L (Metric)	37.7
Fixation Method	Screw Mounting and Adhesive
Width W (Imperial)	1.49
Width W (Metric)	37.7
Cable Ties	T18 - T150
Height H (Imperial)	.28
Height H (Metric)	7.10
Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.9
Mounting Hole Diameter D (Imperial)	0.19
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Diameter D Max (Metric)	4.8
Mounting Hole Centers (Imperial)	1.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V2 (excluding adhesive)
Adhesive Operating Temperature	-4°F to +122°F (-20°C to +50°C)
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.