

Specification Sheet

Part Number: S2CM258HIRHSH1



2-Way Saddle Mount, 3.5" Max Bundle Diameter, 0.25" Stud Diameter, PA66HIRHS, Gray, 500/pkg

Article Number	151-29400
Type	S2CM25
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">•Separates bundles from wear and chafing, providing additional longevity.•Hexagonal retention feature (S2HM25) captures a bolt or nut requiring tool access from the back side only. •A socket counterbore allows securing with a socket wrench from the top side for use with a weld stud or bolt (S2CM25.)•Made from impact modified, heat stabilized, UV resistant material making it ideal for heavy duty applications.
Quantity Per	bag

Product Description

HellermannTyton's saddle mount can be installed between two bundles (such as wires, cables, hoses, tubing, conduit, etc.) to separate them and prevent chafing and wear. Fastened to a frame rail or mounting bracket, the H-profile on the saddle mount provides a tight circumferential loop on large and small bundles. Cable ties up to 1/2" wide are used to secure the bundles.

Short Description	2-Way Saddle Mount, 3.5" Max Bundle Diameter, 0.25" Stud Diameter, PA66HIRHS, Gray, 500/pkg
Global Part Name	S2CM25-PA66HIRHS-GY
Length L (Imperial)	1.80
Length L (Metric)	45.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	1.2
Width W (Metric)	30.0
Cable Ties	T50 - T250
Height H (Imperial)	0.90
Height H (Metric)	23.0
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.24
Mounting Hole Diameter D (Metric)	6.35 mm (hexagonal) 6.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24

Mounting Hole Diameter D Max (Metric)

6.0

Stud Diameter (Metric)

6.35 mm

Stud Diameter (Imperial)

0.25

Material

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut

PA66HIRHS

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

