

Specification Sheet

Part Number: CTAP210C2



Cable Tie Anchor Mount, .20 x.70" Hole Dia, .20" Max Tie Width, PA66, White, 100/pkg

Article Number	151-30200
Type	CTAP2
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• Mount provides a "stand-off" for perpendicular bundles.• Secures with a single screw with the option of an additional screw, providing extra stability.
Quantity Per	bag
Product Description	HellermannTyton cable tie anchor plates are designed as a "stand-off" mount for perpendicular wire bundles. These mounts offer an elongated mounting hole for easier alignment of wire bundles. The mounts are installed quick and easy by securing a single screw, with the option of an additional screw for maximum stability.
Short Description	Cable Tie Anchor Mount, .20 x.70" Hole Dia, .20" Max Tie Width, PA66, White, 100/pkg

Global Part Name

CTAP2-PA66-WH

Length L (Imperial)

2.13

Length L (Metric)

54.1

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

0.5

Width W (Metric)

12.7

Cable Ties

T18 - T50

Height H (Imperial)

.14

Height H (Metric)

3.50

Cable Tie Width Max (Imperial)

0.2

Cable Tie Width Max (Metric)

5.0

Mounting Hole Diameter D (Imperial)

0.2 x 0.7

Mounting Hole Diameter D (Metric)

5.0 x 19.0 mm

Mounting Hole Diameter D Max (Metric)

19.0

Material

Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

ROHS Complaint Yes

Certification/Specification WEB UL-ZODZ2.E64139

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

Content Unit(BMEcat) pcs.

Weight (Metric) 1.994