

Specification Sheet

Part Number: CTM010C2



Cable Tie Anchor Mount, .58" x .37", .15" Hole Dia, .2" Max Tie Width, PA66, White, 100/pkg

Article Number	151-30303
Type	CTM0
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• Designed for use with 18 through 50 pound cable ties to provide stability when securing bundles.• Secures with a single screw providing quick installation.
Quantity Per	bag
Product Description	HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw.
Short Description	Cable Tie Anchor Mount, .58" x .37", .15" Hole Dia, .2" Max Tie Width, PA66, White, 100/pkg

Global Part Name

CTM0-PA66-WH

Length L (Imperial)

0.58

Length L (Metric)

14.7

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

0.37

Width W (Metric)

9.4

Cable Ties

T18 - T50

Height H (Imperial)

.27

Height H (Metric)

6.90

Cable Tie Width Max (Imperial)

0.2

Cable Tie Width Max (Metric)

5.0

Mounting Hole Diameter D (Imperial)

0.15

Mounting Hole Diameter D (Metric)

3.8 mm

Mounting Hole Diameter D Max (Metric)

3.8

Material

Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB UL | ANSI/UL 62275 UL | ANSI/UL 746B UL | ANSI/UL 1565

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

Content Unit(BMEcat) pcs.