

Specification Sheet

Part Number: CTM20M4



Cable Tie Anchor Mount, .86" x .61", .18" Hole Dia, .31" Max Tie Width, PA66, Black, 1000/pkg

Article Number	151-30501
Type	CTM2
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Designed for use with 18 through 120 pound cable ties to provide stability when securing bundles.• Secures with a single screw providing quick installation.
Quantity Per	bag
Product Description	HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw.
Short Description	Cable Tie Anchor Mount, .86" x .61", .18" Hole Dia, .31" Max Tie Width, PA66, Black, 1000/pkg

Global Part Name

CTM2-PA66-BK

Length L (Imperial)

0.86

Length L (Metric)

21.8

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

0.61

Width W (Metric)

15.5

Cable Ties

T18 - T120

Height H (Imperial)

.37

Height H (Metric)

9.40

Cable Tie Width Max (Imperial)

0.31

Cable Tie Width Max (Metric)

7.9

Mounting Hole Diameter D (Imperial)

0.18

Mounting Hole Diameter D (Metric)

4.6 mm

Mounting Hole Diameter D Max (Metric)

4.6

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 V2

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

UL 62275

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988