

Specification Sheet

Part Number: FC1.2K2



Flat Ribbon Clamp, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Article Number	154-00011
Type	FC1.2
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">•Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable.•Releasable for easy access to cables when necessary.
Quantity Per	bag
Product Description	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.
Short Description	Flat Ribbon Clamp, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Global Part Name

FC1.2-PA66-GY

Length L (Imperial)

0.75

Length L (Metric)

19.0

Width W (Imperial)

1.50

Width W (Metric)

38.1

Height H (Imperial)

0.50

Height H (Metric)

12.7

Mounting Hole Diameter D (Imperial)

0.156

Mounting Hole Diameter D (Metric)

4.0 mm

Mounting Hole Diameter D Min (Imperial)

0.156

Mounting Hole Diameter D Max (Imperial)

0.156

Mounting Hole Diameter D Max (Metric)

4.0

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Flammability

UL 94 V2

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988