

Specification Sheet

Part Number: FC1.2AK2



Flat Ribbon Cable Clamp, Adhesive, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Article Number	154-00013
Type	FC1.2A
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none">•Adjustable height feature allows the clamp to close to the exact height of the ribbon cable.•Releasable for easy access to cables when necessary.
Quantity Per	bag
Product Description	HellermannTyton's flat ribbon clamps route, protect, and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.
Short Description	Flat Ribbon Cable Clamp, Adhesive, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Global Part Name

FC1.2A-PA66-GY

Length L (Imperial)

0.75

Length L (Metric)

19.0

Width W (Imperial)

1.5

Width W (Metric)

38.1

Height H (Imperial)

0.5

Height H (Metric)

12.7

Mounting Hole Diameter D (Imperial)

0.157

Mounting Hole Diameter D (Metric)

4.0 mm

Mounting Hole Diameter D Min (Imperial)

0.157

Mounting Hole Diameter D Max (Imperial)

0.157

Mounting Hole Diameter D Max (Metric)

4.0

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Adhesive

Acrylate with base of polyurethane foam

Flammability

UL 94 V2 (excluding adhesive)

Adhesive Operating Temperature

to +230°F (+110°C)

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988