

## Specification Sheet

Part Number: FC2.2K2



Flat Ribbon Clamp, 2.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

<b>Article Number</b>	154-00015
<b>Type</b>	FC2.2
<b>Color</b>	Gray (GY)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable.</li><li>•Releasable for easy access to cables when necessary.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.
<b>Short Description</b>	Flat Ribbon Clamp, 2.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

**Global Part Name**

FC2.2-PA66-GY

**Length L (Imperial)**

0.75

**Length L (Metric)**

19.0

**Width W (Imperial)**

2.60

**Width W (Metric)**

66.0

**Height H (Imperial)**

0.50

**Height H (Metric)**

12.7

**Mounting Hole Diameter D (Imperial)**

0.156

**Mounting Hole Diameter D (Metric)**

4.0 mm

**Mounting Hole Diameter D Min (Imperial)**

0.156

**Mounting Hole Diameter D Max (Imperial)**

0.156

**Mounting Hole Diameter D Max (Metric)**

4.0

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Flammability**

UL 94 V2

**Operating Temperature (Metric)**

-40°F to +185°F (-40°C to +85°C)

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

50

**Package Quantity (Metric)**

50

**Customs Number**

3926909988