

Specification Sheet

Part Number: MSMP5/69C2



Mounting plates allow multiple bundles to run parallel.

The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Cable Tie Mounting Plate, 8.08 x .62", 0.15" Hole Dia, 0.3" Max Tie Width, PA66, Natural, 100/pkg

Article Number 154-00018

Type MSMP5/6

Color Natural (NA)

Quantity Per bag

Product Description HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots.

Short Description Cable Tie Mounting Plate, 8.08 x .62", 0.15" Hole Dia, 0.3" Max Tie Width, PA66, Natural, 100/pkg

Global Part Name MSMP5/6-PA66-NA

Length L (Imperial)	8.08
Length L (Metric)	205.23
Fixation Method	Screw Mount
Width W (Imperial)	0.62
Width W (Metric)	15.8
Cable Ties	T18 - T120
Height H (Imperial)	0.21
Height H (Metric)	5.30
Cable Tie Width Max (Imperial)	0.3
Cable Tie Width Max (Metric)	7.6
Mounting Hole Diameter D (Imperial)	0.15
Mounting Hole Diameter D (Metric)	3.8 mm
Mounting Hole Diameter D Max (Metric)	3.8
Mounting Hole Centers (Imperial)	1.5
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988