

Specification Sheet

Part Number: 155-01600



Standoff Bundling Clip, 1.6" Long, Fixing Hole Dia .26"-.28", PA66HIRHS Black 500/pkg

Article Number	155-01600
Type	STAND-OFF-CLIP-2
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Clip can be installed by hand – no need for hardware or tools.•Design provides low insertion and high extraction force, for simple, secure performance.•Clip keeps bundle away from areas that could cause damage due to rubbing.
Quantity Per	bag

Product Description

Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Short Description	Standoff Bundling Clip, 1.6" Long, Fixing Hole Dia .26"-.28",PA66HIRHS Black 500/pkg
Global Part Name	STAND-OFF-CLIP-2-PA66HIRHS-BK
Length L (Imperial)	1.6
Length L (Metric)	40.0
Offset Length(Imperial)	0.98
Offset Length(Metric)	25.0
Fixation Method	Arrowhead
Panel Thickness Min(Imperial)	0.02
Panel Thickness Max(Imperial)	0.06
Panel Thickness Min (Metric)	0.40
Panel Thickness Max (Metric)	1.6
Mounting Hole Diameter D (Imperial)	0.26 - 0.27
Mounting Hole Diameter D (Metric)	6.5 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.26
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.75