

Specification Sheet

Part Number: 155-05400



1-Piece Cable Tie/Oval Stud Mount, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg

Article Number	155-05400
Type	T50SOSSB5HEC
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Oval mount design pushes on easy by hand without the need for tools.• Design provides low insertion and high extraction force.
Quantity Per	bag
Product Description	The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables
Short Description	1-Piece Cable Tie/Oval Stud Mount, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg

Global Part Name

T50SOSSB5HEC-PA66HS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

170

Length L (Imperial)

6.0

Length L (Metric)

160

Fixation Method

Weld Stud Fixing

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.04

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.0

Thickness T (Imperial)

0.05

Thickness T (Metric)	1.35
Stud Length Max (Imperial)	0.63
Stud Length Max (Metric)	16.0
Stud Length Min (Metric)	11.0
Stud Diameter (Metric)	5.0 mm
Stud Diameter (Imperial)	0.2
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

2.75