

## Specification Sheet

Part Number: 155-11601



Bundling Clip with Arrowhead, 2.17" Long, 0.06" - 0.12" Panel Thickness, PA66HIRHS, Black, 500/pkg

<b>Article Number</b>	155-11601
<b>Type</b>	BCSFT6.5 16-3MD
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
<b>Short Description</b>	Bundling Clip with Arrowhead, 2.17" Long, 0.06" - 0.12" Panel Thickness, PA66HIRHS, Black, 500/pkg

Global Part Name

BCSFT6.5 16-3MD-PA66HIRHS-BK

Length L (Imperial)

2.17

Length L (Metric)

55.0

Fixation Method

Arrowhead

Width W (Imperial)

0.32

Width W (Metric)

8.0

Height H (Imperial)

0.55

Height H (Metric)

14.0

Panel Thickness Min(Imperial)

0.06

Panel Thickness Max(Imperial)

0.12

Panel Thickness Min (Metric)

1.5

Panel Thickness Max (Metric)

3.0

Mounting Hole Diameter D (Metric)

6.3 - 6.7 mm

Mounting Hole Diameter D Min (Imperial)

0.25

Mounting Hole Diameter D Max (Imperial)

0.26

Mounting Hole Diameter D Max (Metric)

6.7

Disc Diameter(Metric)

16.0

<b>Disc Diameter (Imperial)</b>	0.63
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Shortcut</b>	PA66HIRHS
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.
<b>Weight (Metric)</b>	1.2

