

Specification Sheet

Part Number: 155-30702



Connector Clip w/Fir Tree, 0.7 - 5.1 mm Panel Thickness, 6.4 - 7.1 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Article Number

155-30702

Type

FT6LG.YAZ.CONNECT-TS

Color

Black (BK)

Features & Benefits

- Head design contains clamping rails to provide full circumferential compression around bundles.
- Bent tail allows for quick insertion into head.

Quantity Per

bag

Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description

Connector Clip w/Fir Tree, 0.7 - 5.1 mm Panel Thickness, 6.4 - 7.1 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Global Part Name

FT6LG.YAZ.CONNECT-TS-PA66HIRHS-BK

Fixation Method

Fir Tree

Panel Thickness Min(Imperial)

0.028

Panel Thickness Max(Imperial)

0.2

Panel Thickness Min (Metric)

0.7

Panel Thickness Max (Metric)

5.1

Mounting Hole Diameter D (Imperial)

0.25 - 0.28

Mounting Hole Diameter D (Metric)

6.4 - 7.1 mm

Mounting Hole Diameter D Min (Imperial)

0.25

Mounting Hole Diameter D Max (Imperial)

0.28

Mounting Hole Diameter D Max (Metric)

7.1

Disc Diameter(Metric)

16

Disc Diameter (Imperial)

0.63

Material

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut

PA66HIRHS

Flammability

UL 94 HB

Operating Temperature (Metric)

-40°F to +221°F (-40°C to +105°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Package Quantity(Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.93