

## Specification Sheet

Part Number: 155-30902



Standoff Bundling Clip, 2.2" Long, Panel Thickness .02"–.03", PA66HIRHS, Black, 500/box

|                     |  |
|---------------------|--|
| Article Number      | 155-30902  |
| Type                | SOC4 M.FT6   |
| Color               | Black (BK)   |
| Features & Benefits | <ul style="list-style-type: none"><li>•Clip can be installed by hand – no need for hardware or tools.</li><li>•Design provides low insertion and high extraction force, for simple, secure performance.</li><li>•Clip keeps bundle away from areas that could cause damage due to rubbing.</li></ul> |
| Quantity Per        | bag  |

### Product Description

Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

|  |   |
|--|---|
| <b>Short Description</b>                       | Standoff Bundling Clip, 2.2" Long, Panel Thickness .02"-.03", PA66HIRHS, Black, 500/box |
| <b>Global Part Name</b>                        | SOC4 M.FT6-PA66HIRHS-BK   |
| <b>Length L (Imperial)</b>                     | 2.2   |
| <b>Length L (Metric)</b>                       | 55.0  |
| <b>Offset Length(Imperial)</b>                 | 0.79  |
| <b>Offset Length(Metric)</b>                   | 20.0  |
| <b>Fixation Method</b>                         | Fir Tree  |
| <b>Height H (Imperial)</b>                     | 0.54  |
| <b>Height H (Metric)</b>                       | 13.72   |
| <b>Panel Thickness Min(Imperial)</b>           | 0.03  |
| <b>Panel Thickness Max(Imperial)</b>           | 0.2   |
| <b>Panel Thickness Min (Metric)</b>            | 0.7   |
| <b>Panel Thickness Max (Metric)</b>            | 5.1   |
| <b>Mounting Hole Diameter D (Imperial)</b>     | 0.25 - 0.28   |
| <b>Mounting Hole Diameter D (Metric)</b>       | 6.5 - 7.0 mm  |
| <b>Mounting Hole Diameter D Min (Imperial)</b> | 0.283   |

**Mounting Hole Diameter D Max (Imperial)**

0.28

**Mounting Hole Diameter D Max (Metric)**

7.0

**Material**

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

**Material Shortcut**

PA66HIRHS

**Flammability**

UL 94 HB

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

1.6

