

## Specification Sheet

Part Number: 155-38102



Connector Clip w/Fir Tree, 0.75 - 1.5 mm Panel Thickness, 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Article Number	155-38102
Type	YCC-FT6-S
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Head design contains clamping rails to provide full circumferential compression around bundles.</li><li>•Bent tail allows for quick insertion into head.</li></ul>
Quantity Per	bag

### Product Description

Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

**Short Description**

Connector Clip w/Fir Tree, 0.75 - 1.5 mm Panel Thickness, 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 500/ pkg

**Global Part Name**

YCC-FT6-S-PA66HIRHS-BK

**Fixation Method**

Fir Tree

**Panel Thickness Min(Imperial)**

0.04

**Panel Thickness Max(Imperial)**

0.06

**Panel Thickness Min (Metric)**

0.75

**Panel Thickness Max (Metric)**

1.5

**Mounting Hole Diameter D (Imperial)**

0.26 - 0.28

**Mounting Hole Diameter D (Metric)**

6.5 - 7.0 mm

**Mounting Hole Diameter D Min (Imperial)**

0.26

**Mounting Hole Diameter D Max (Imperial)**

0.275

**Mounting Hole Diameter D Max (Metric)**

7.0

**Disc Diameter(Metric)**

16

**Disc Diameter (Imperial)**

0.63

**Material**

Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

**Material Shortcut**

PA66HIRHS

**Flammability**

UL 94 HB

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

**Content Unit(BMEcat)**

pcs.

**Weight (Metric)**

0.78