

Specification Sheet

Part Number: 156-00155



1-Piece Cable Ties with Pipe Clip, Diameter .26"-.31", 6.0" Long, PA66HS/PA66HIRHS, Black, 500/pkg

Article Number	156-00155
Type	T50SVC6.5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Design provides quick and easy installation by hand without the need for tools.• Multiple bundle diameters available for all different ranges of bundles.• Clip allows 360 degrees of rotation to attach in any orientation.
Quantity Per	bag

Product Description

HellermannTyton's simple to use fixing tie allows the attaching of wires or hoses to an existing harness. This allows 360 degree rotation, and the ability to be oriented in any direction in relation to the main harness. This is ideally suited for any application in which the wire or hose can move in relation to the fixing point.

Short Description	1-Piece Cable Ties with Pipe Clip, Diameter .26"-.31", 6.0" Long, PA66HS/PA66HIRHS, Black, 500/pkg
Global Part Name	T50SVC6.5-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.1
Length L (Metric)	155.0
Fixation Method	Omega Clips
Identification Plate Position	none
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.4
Bundle Diameter Max (Metric)	35.0
Mounting Hole Diameter D (Imperial)	0.26 - 0.31

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.66