

Specification Sheet

Part Number: 156-00591



2-Piece Cable Tie & Edge Clip, 8.0" Long, EC20, 3-6 mm Panel, 50lb, PA66UV/PA66HIRHSUV, Black, 100/pkg

Article Number

156-00591

Type

T50REC20

Color

Black (BK)

Features & Benefits

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Quantity Per

bag

Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description

2-Piece Cable Tie & Edge Clip, 8.0" Long, EC20, 3-6 mm Panel, 50lb, PA66UV/PA66HIRHSUV, Black, 100/pkg

Global Part Name

T50REC20-PA66UV/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.0

Length L (Metric)

202.0

Fixation Method

EdgeClip, top, assembled, 2 piece

Identification Plate Position

none

Variant

Inside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.0

Thickness T (Imperial)

0.05

Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Height H (Metric)	1.2
Panel Thickness Min(Imperial)	0.12
Panel Thickness Max(Imperial)	0.24
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	6.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 UV-stabilized (PA66UV)
Material Shortcut	PA66HIRHS PA66UV
Material Cable Tie	Polyamide 6.6 UV-stabilized (PA66UV)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C) -40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)