

Specification Sheet

Part Number: 156-00799



2-Piece Cable Tie & Edge Clip, 6.0" Long, EC20, 1–3 mm Panel, 30lb, PA66HS, Black, 500/bag

Article Number	156-00799
Type	T30REC20
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.• Edge Clip provides low insertion force and high extraction force ideal for assembly environments.• Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
Quantity Per	bag

Product Description

This cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description

2-Piece Cable Tie & Edge Clip, 6.0" Long, EC20, 1–3 mm Panel, 30lb, PA66HS, Black, 500/bag

Global Part Name

T30REC20-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135

Length L (Imperial)

6.0

Length L (Metric)

150.0

Fixation Method

EdgeClip, top, assembled, 2 piece

Identification Plate Position

none

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

1.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

32.0

Thickness T (Imperial)

0.04

Height H (Imperial)	0.04
Height H (Metric)	1.1
Panel Thickness Min(Imperial)	0.12
Panel Thickness Max(Imperial)	0.24
Panel Thickness Min (Metric)	3.00
Panel Thickness Max (Metric)	6.00
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

