

## Specification Sheet

Part Number: 156-00877



Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC23, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number	156-00877
Type	T50ROSEC23
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.</li><li>•Edge Clip provides low insertion force and high extraction force ideal for assembly environments.</li><li>•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.</li><li>•Cable tie is outside serrated to reduce bundle chafing.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

<b>Short Description</b>	Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC23, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg
<b>Global Part Name</b>	T50ROSEC23-PA66HS/PA66HIRHS-BK
<b>Minimum Tensile Strength (Imperial)</b>	50.0
<b>Minimum Tensile Strength (Metric)</b>	225
<b>Length L (Imperial)</b>	8.0
<b>Length L (Metric)</b>	200.0
<b>Fixation Method</b>	EdgeClip, sideways, assembled, 2 piece
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Variant</b>	Outside Serrated
<b>Width W (Imperial)</b>	0.18
<b>Width W (Metric)</b>	4.6
<b>Bundle Diameter Min (Imperial)</b>	0.20
<b>Bundle Diameter Min (Metric)</b>	1.5
<b>Bundle Diameter Max (Imperial)</b>	2.0
<b>Bundle Diameter Max (Metric)</b>	45.0

<b>Thickness T (Imperial)</b>	0.05
<b>Thickness T (Metric)</b>	1.3
<b>Height H (Imperial)</b>	0.05
<b>Height H (Metric)</b>	1.3
<b>Panel Thickness Min(Imperial)</b>	0.12
<b>Panel Thickness Max(Imperial)</b>	0.24
<b>Panel Thickness Min (Metric)</b>	3.0
<b>Panel Thickness Max (Metric)</b>	6.0
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HIRHS PA66HS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988

**Weight (Metric)**

2.73