

Specification Sheet

Part Number: 156-01092



LOC Locking Clamp, 10–14 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 3000/ctn

Article Number

156-01092

Type

T50RLOC10-14-SET

Color

Black (BK)

Features & Benefits

- The 360 degree locking enclosure and cable tie dynamically fit a range of bundle sizes.
- Clamp can be opened for bundle maintenance.
- Low-profile release tab won't interfere with bundle or nearby routing.
- The two bundles are allowed to rotate up to 90 degrees from one another.

Quantity Per

carton

Product Description

HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.

Short Description

LOC Locking Clamp, 10–14 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 3000/ctn

Global Part Name

T50RLOC10-14-SET-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

1.09

Length L (Metric)

27.6

Fixation Method

Omega Clips

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.47

Width W (Metric)

12.0

Bundle Diameter Min (Imperial)

0.39

Bundle Diameter Min (Metric)

10.0

Bundle Diameter Max (Imperial)

0.55

Bundle Diameter Max (Metric)

14.0

Height H (Imperial)

1.08

Height H (Metric)	27.4
Depth D (imperial)	0.47
Depth D (metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	2.8

Weight (Imperial)

0.1

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)