

## Specification Sheet

Part Number: 156-01339



**Article Number**

156-01339

**Type**

T50SVCOC15-18

**Color**

Black (BK)

**Features & Benefits**

- Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.
- Clip is reusable, making relocation or adjustments simple.
- All-in-one bundling and mounting solution reduces costs.

**Quantity Per**

bag

**Product Description**

HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

**Short Description**

1-Piece Cable Ties with Pipe Clip, 6.0" Long, Attaches to Diameter .59" - .71", PA66HS, Black, 500/pkg

Global Part Name

T50SVCOC15-18-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

222

Length L (Imperial)

6.1

Length L (Metric)

155.0

Fixation Method

Omega Clips

Identification Plate Position

none

Tie Closure

plastic pawl

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.08

Bundle Diameter Min (Metric)

2.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.0

Thickness T (Metric)

1.35

<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HIRHS PA66HS
<b>Material Cable Tie</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	500
<b>Package Quantity (Metric)</b>	500
<b>Customs Number</b>	3926909988