

Specification Sheet

Part Number: 156-01341



1-Piece Cable Ties with Pipe Clip, 6.0" Long, Attaches to Diameter .75" - .96", PA66HS, Black, 500/pkg

Article Number	156-01341
Type	T50SVCOC19-24.5
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.•Clip is reusable, making relocation or adjustments simple.•All-in-one bundling and mounting solution reduces costs.
Quantity Per	bag
Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	1-Piece Cable Ties with Pipe Clip, 6.0" Long, Attaches to Diameter .75" - .96", PA66HS, Black, 500/pkg

Global Part Name

T50SVCOC19-24.5-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

222

Length L (Imperial)

6.1

Length L (Metric)

155.0

Fixation Method

Omega Clips

Identification Plate Position

none

Tie Closure

plastic pawl

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.08

Bundle Diameter Min (Metric)

2.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.0

Thickness T (Metric)

1.35

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988