

## Specification Sheet

Part Number: 156-01513



2-Piece Cable Tie/Fir Tree Mount, 7.9"L, .22"-.25" Mounting Hole, 100lb, PAEK, Beige, 500/bag

Article Number	156-01513
Type	PAT100LFT6LG
Color	Beige (BGE)
Features & Benefits	<ul style="list-style-type: none"><li>•Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.</li><li>•Fir tree provides low insertion effort yet demonstrates high extraction resistance.</li><li>•Disc feature prevents rattling in high-vibration applications and protects against debris ingress.</li></ul>
Quantity Per	bag
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

**Short Description**

2-Piece Cable Tie/Fir Tree Mount, 7.9"L, .22"-.25" Mounting Hole, 100lb, PAEK, Beige, 500/bag

**Global Part Name**

PAT100LFT6LG-PAEK-BGE

**Minimum Tensile Strength (Imperial)**

100.0

**Minimum Tensile Strength (Metric)**

445

**Length L (Imperial)**

7.9

**Length L (Metric)**

200.7

**Fixation Method**

Fir Tree

**Identification Plate Position**

none

**Tie Closure**

plastic pawl

**Width W (Imperial)**

0.33

**Width W (Metric)**

8.0

**Bundle Diameter Min (Imperial)**

0.06

**Bundle Diameter Min (Metric)**

1.5

**Bundle Diameter Max (Imperial)**

2.0

**Bundle Diameter Max (Metric)**

50.8

**Height H (Imperial)**

.75

<b>Height H (Metric)</b>	19.20
<b>Panel Thickness Min(Imperial)</b>	0.05
<b>Panel Thickness Max(Imperial)</b>	0.236
<b>Panel Thickness Min (Metric)</b>	1.25
<b>Panel Thickness Max (Metric)</b>	6.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.22 - 0.25
<b>Mounting Hole Diameter D (Metric)</b>	5.6 - 6.4 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.22
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.25
<b>Mounting Hole Diameter D Max (Metric)</b>	6.4
<b>Disc Diameter(Metric)</b>	18.6
<b>Disc Diameter (Imperial)</b>	0.73
<b>Material</b>	Polyaryletherketone (PAEK)
<b>Material Shortcut</b>	PAEK
<b>Flammability</b>	UL 94 V0
<b>Halogen free</b>	No

**Operating Temperature (Metric)**

-67°F to +392°F (-55°C to +200°C)

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988