

Specification Sheet

Part Number: 156-01614



LOC Locking Clamp, 20-25 mm, to MOC Clip, 8 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01614
Type	MOC8LOC20-25
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.• Controlled flex and angled entry promote easy installation.• Independent rotation allows for adjustable routing orientation.
Quantity Per	carton
Product Description	The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	LOC Locking Clamp, 20-25 mm, to MOC Clip, 8 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

MOC8LOC20-25-PA66HIRHSUV-BK

Length L (Imperial)

2.06

Length L (Metric)

52.4

Variant

Clip to Clamp

Width W (Imperial)

0.47

Width W (Metric)

12.00

Bundle Diameter Min (Imperial)

0.79

Bundle Diameter Min (Metric)

20.0

Bundle Diameter Max (Imperial)

0.98

Bundle Diameter Max (Metric)

25.0

Height H (Imperial)

1.53

Height H (Metric)

38.9

Depth D (imperial)

0.47

Depth D (metric)

12.0

Material

Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut

PA66HIRHSUV

Flammability

UL 94 HB

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +230°F (-40°C to +110°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

1000

Package Quantity (Metric)

1000

Customs Number

3926909988

Weight (Metric)

4.63

Weight (Imperial)

0.16